

CIRCULUM®

K-200p

DESCRIPTION

K-200p is an uncoated expandable polystyrene grade containing pentane as a blowing agent. The products are delivered in the form of spherical beads with a bulk density of about 0.6 g/cm³. **K-200p** is available in 1100 kg octabins.

APPLICATIONS

The properties of **K-200p** make it suitable for loose beads applications. **K-200p** can be used for some block moulding applications.

PROCESSING

The processing conditions of **K-200p** depend on the combination of the product and processing equipment used. Optimal settings have to be adjusted for each combination. Some general processing conditions are given below:

- | | |
|---------------------|--|
| Prefoaming | The steam has to be saturated at a temperature of 100–110 °C. To reach densities below 15 kg/m ³ , batch prefoamer is recommended and with a continuous prefoamer to prefoam twice. To reach higher densities (>25 kg/m ³) it is recommended to mix the steam with air. |
| Conditioning | Depends on the density. The higher the density the longer the conditioning time. Generally 12–24 hours is recommended. When prefoaming in two steps, a conditioning time of 4–6 hours between the first and the second step is optimal but can be a bit longer. |
| Moulding | <p>The machine should be fed with saturated steam with a maximum pressure of about 2 bar.</p> <p>The steaming time depends on the equipment used as well as the size and required strength of the final product. Therefore, all machines have to be adjusted individually. Equipment using vacuum is recommended to reduce cycle times and to increase product strength.</p> |
| Cutting | Hot wire cutting (oscillating or stationary wires) is recommended. Temperature of the wires should be about 200–300 °C. |

TECHNICAL INFORMATION

TYPICAL PHYSICAL PROPERTIES

Raw material

| | <u>Value</u> | <u>Unit</u> | <u>Test method</u> |
|-----------------------------|--------------|-------------|--------------------|
| Pentane content | 5.5– 6.5 | % | Gas chromatography |
| Monomer level | < 0.1 | % | Gas chromatography |
| Main bead size distribution | 1.4 – 2.5 | mm | Image analyser |

STORAGE

K-200p should be stored at below 20 °C. Protect from direct sunlight and other weather conditions (rain, wind, frost etc.). Keep away from any source of ignition. The storage time should not exceed three months. After opening of the packaging, it should be used as soon as possible.

SAFETY

In transport **K-200p** is classified according to European regulations for product transport: Substance number UN2211, Class 9.

In processing avoid generating dust. All equipment should be properly earthen. Releases pentane during processing which might form a flammable/explosive vapour-air mixture. Use proper ventilation and keep away from any source of ignition. A Safety Data Sheet is available on request.

RECYCLING

K-200p is suitable for recycling using modern methods of grinding, cleaning and regranulation. In-house production waste should be kept clean to facilitate direct recycling.

Please contact your BEWiSynbra RAW representative for more details on various aspects of safety, recovery and disposal of the product.

This information is not to be taken as a warranty or representation for which BEWiSynbra RAW Oy assumes legal responsibility nor as permission or recommendation to practice any patented invention without a license. It is offered solely for your consideration, investigation, verification and shall form no part of any contract with a customer.

La présente documentation n'engage pas notre responsabilité et n'autorise en aucune façon l'usage sans contrat de licence d'inventions brevetées. Les termes du présent rapport doivent être considérés comme une simple indication, sujette aux vérifications d'usage.

Bei diesen Angaben handelt es sich weder um eine Garantie-Erklärung oder Darstellung, für die wir eine rechtliche Haftung übernehmen, noch um eine Erlaubnis oder Empfehlung, irgendeine patentierte Erfindung ohne Lizenz auszuwerten. Die Informationen werden Ihnen lediglich zu Ihrer Erwägung, Untersuchung und Überprüfung übermittelt und sind nicht Bestandteil von Verträgen mit Kunden.

Uppgifter i datablad, broschyrer och annat informationsmaterial ges som vägledning och är ej bindande för BEWiSynbra RAW Oy.

Tässä esitteessä ja muussa tiedotusaineistossa annetut tekniset tiedot ovat suuntaa antavia, eivätkä ne ole BEWiSynbra RAW Oy:tä sitovia.

Le informazioni contenute nelle schede tecniche, bollettini ed altro materiale informativo corrispondono all'attuale livello di conoscenza

e intendono fornire indicazioni sui prodotti BEWiSynbra RAW Oy e le loro possibilità di impiego. Non sono pertanto da intendersi come garanzia.